



## MATERIAL SPECIFICATION & INSTALLATION GUIDE

Fully compliant with AS1428.1-2009  
Disability Standard

### ML 835 ~ DUAL LOCKABLE TOILET ROLL HOLDERS




#### MATERIAL SPECIFICATIONS:

#304 Grade Stainless Steel, Rolled & Seamed Edges / Lockable / Supplied With Fixings

#### DIMENSIONS:

~ 280mm W x 135mm H x 130mm D



#### INSTALLATION GUIDE:

1. May be subject to Australian Building Code Regulations for height/location fixing and/or subject to placement as per architectural drawings, which in all cases is the responsibility of the installer re compliance.
2. Locate height on wall and mark via internal fixing holes onto wall, ensuring unit is level and even. Measure/Check Twice ... Drill Once
3. Drill holes and loosely secure to wall surface using supplied fixings or suitable alternative fasteners
4. Check level and tighten fixings/fasteners

**NOTE:** Toilet Paper (not included but recommended to use quality standard 3 ply toilet rolls) is loaded with the loose leaf facing towards the rear, with the initial roll forced past the internal spring clip; reload by removing used core, then by way of placing fingers in side holes/slots & drawing upper roll down

*These units should only be installed by a competent tradesperson and Metlam Australia takes no responsibility for any damage to walls or fixtures due to incorrect installation.*